

Flat cylinder DZF-50-125-P-A

Part number: 164073

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 125 mm |
| Piston diameter | 50 mm Equivalent diameter |
| Piston rod thread | M10 |
| Torsional backlash at piston rod +/- | 0.5 deg |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | optional |
| Mode of operation | Double-acting |
| Design | Piston Piston rod |
| Position detection | Via proximity switch |
| Protection against torque/guide | Oval piston |
| Operating pressure | 0.1 MPa...1 MPa 1 bar...10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C...80 °C |
| Impact energy in end positions | 0.64 J |
| Max. torque for protection against torsion | 1.2 Nm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 990 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 1178 N |
| Moving mass for 0 mm stroke | 219 g |
| Additional moving mass per 10 mm stroke | 25 g |
| Additional weight per 10 mm stroke | 64 g |
| Basic weight for 0 mm stroke | 854 g |
| Type of mounting | Via female thread With accessories Either: |
| Pneumatic connection | G1/4 |
| Material cover | Die-cast aluminium |

| Feature | Value |
|----------------------|----------------------------------|
| Material seals | NBR TPE-U(PU) |
| Material housing | Anodised wrought aluminium alloy |
| Material piston seal | NBR |
| Material piston rod | High-alloy steel |