


Ball valve

VZBA-3/4"-GGG-63-32T-F0405-V4V4T

Part number: 1692226

FESTO



Data sheet

Feature	Value
Design	3-way ball valve T-hole
Type of actuation	Mechanical
Sealing principle	Soft
Mounting position	optional
Type of mounting	In-line installation
Connection Process valve	Rp3/4
Switching position indicator	Slot direction = flow direction
Flange hole pattern	F04 F05
Inside diameter	16 mm
Nominal size DN	20
Valve function	3/2
Manual override	None
Flow direction	Reversible
Nominal pressure PN	63
Actuating torque	18 Nm
Based on standard	EN 10226-1 ISO 5211
Medium	Compressed air to ISO 8573-1:2010 [-:...] Inert gases Water – no water vapour Neutral fluids Other media on request
Media temperature	-10 °C...200 °C
Flow rate Kv T hole angled	4.8 m³/h
Flow rate Kv T hole straight	8.3 m³/h
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material housing	High-alloy stainless steel

Feature	Value
Material number housing	1.4408
Material seals	PTFE PTFE reinforced
Material ball	High-alloy stainless steel
Material number ball	1.4408
Material shaft	High-alloy stainless steel
Material number shaft	1.4401
Product weight	1000 g
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class CRC	3 - high corrosion stress