

proximity sensor SMEO-8E-M12-LED-230



Part number: 171160
Product to be discontinued

FESTO

Electric, with reed contact, for drives with T-slot, without mounting kit, with M12 plug.

Separate mounting component SMB-8E required (part no. 178230)

Type to be discontinued. Available until 2023. See Support Portal for alternative products.



Data sheet

Feature	Value
Design	for T-slot
Conforms to standard	EN 60947-5-2
Authorisation	RCM Mark
CE mark (see declaration of conformity)	to EU directive for EMC to EU directive low-voltage devices in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment To UK instructions for EMC To UK RoHS instructions
Materials note	Conforms to RoHS
Instructions for use	Support / Actuator-sensor overview "The right sensor for the actuator"
Measured variable	Position
Measuring principle	Reed magnetic
Ambient temperature	-20 ... 60 °C
Repetition accuracy	0.2 mm
Switch output	with contact, bipolar Without LED function
Switching element function	Normally open contact
Switch-on time	≤ 2 ms
Switch-off time	0.03 ms
Max. switching frequency	500 Hz
Max. output current	120 mA
Max. contact rating AC	10 VA
Max. contact rating DC	10 W
Voltage drop	3.9 V
Short circuit strength	No
Overload withstand capability	Not available
Operating voltage range AC	3 ... 230 V
Operating voltage range DC	3 ... 250 V
Polarity protected	No
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 1, number of pins/wires	3
Electrical connection 1, type of mounting	Screw lock
Connector exit direction	Lateral
Mounting type	with accessories
Tightening torque	0.5 Nm
Assembly position	Any
Product weight	9 g
Housing colour	Black

Feature	Value
Material housing	Wrought Aluminium alloy TPE-U(PU) High alloy steel, non-corrosive
Operating status display	Yellow LED
Protection class	IP65 IP67
Insulation voltage	250 V
Surge strength	4 kV
PWIS conformity	VDMA24364-B2-L
Degree of contamination	3