

Semi-rotary drive DRVS-32-90-P

Part number: 1845719

FESTO



Data sheet

Feature	Value
Size	32
Cushioning angle	0.5 deg
Swivel angle	0 deg...90 deg
Permissible stop radius	28 mm
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Mode of operation	Double-acting
Design	Vane
Position detection	Via proximity switch
Variants	Spigot shaft
Operating pressure	0.2 MPa...0.8 MPa 2 bar...8 bar
Max. swivel frequency at 0.6 MPa (6 bar, 87 psi)	3 Hz
Repetition accuracy	1 deg
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 5 according to ISO 14644-1
Ambient temperature	0 °C...60 °C
Max. stop force	480 N
Max. axial force	75 N
Max. radial force	200 N
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	10 Nm
Permissible mass moment of inertia	0.02 kgm ²
Product weight	928 g
Type of mounting	Via female thread
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material drive shaft	Nickel-plated steel
Material seals	TPE-U(PU)

Feature	Value
Material housing	Painted die cast aluminium