



tie rod cylinder CRDNG-1 1/4"- -PPV-A-S2

Part number: 185396

FESTO

Corrosion resistant, with double-ended piston rod, based on ISO 15552, NF E 49 003.1 and UNI 10 290, for non-contact sensing. With adjustable end-position cushioning at both ends.



Exemplary representation

Data sheet

Feature	Value
Stroke	2,000 mm
Piston diameter	1 1/4"
Based on the standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Piston-rod end	Male thread
Operating pressure	0.6 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	4 - Very high corrosion stress
Ambient temperature	-20 ... 80 °C
Theoretical force at 6 bar, return stroke	415 N
Theoretical force at 6 bar, advance stroke	415 N
Pneumatic connection	1/8 NPT