

Servo motor

EMME-AS-60-M-LS-AS

Part number: 2089730

FESTO



Data sheet

Feature	Value
Ambient temperature	-10 °C...40 °C
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 90%
Conforms to standard	IEC 60034
Insulation protection class	F
Rating class as per EN 60034-1	S1
Degree of protection	IP21
Electrical connector system	Plug
Note on materials	RoHS-compliant
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Approval	RCM trademark c UL us - Recognized (OL)
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK regulations for electrical equipment
Nominal operating voltage DC	360 V
Nominal voltage DC	360 V
Type of winding switch	Star inside
Number of pole pairs	3
Standstill torque	1.5 Nm
Nominal torque	1.2 Nm
Peak torque	6 Nm
Nominal rotary speed	3000 rpm
Max. rotational speed	4925 rpm
Nominal power rating of motor	380 W
Continuous stall current	1.8 A
Nominal motor current	1.5 A
Peak current	7.2 A
Motor constant	0.8 Nm/A

Feature	Value
Voltage constant, phase-to-phase	51.7 mVmin
Phase-phase winding resistance	9.8 Ohm
Phase-phase winding inductance	16.8 mH
Total mass moment of inertia of output	0.413 kgcm ²
Product weight	1850 g
Permissible axial shaft load	54 N
Permissible radial shaft load	270 N
Rotor position sensor	Absolute single-turn encoder
Rotor position encoder interface	HIPERFACE®
Rotor position sensor, encoder measuring principle	Capacitive
Rotor pos. enc., sin/cosin p/r	16
Rotor pos. encoder, typ. res.	12 bit
Rot. pos. enc., typ. ang. acc.	20 arcmin
Mean time to dangerous failure (MTTFd), subcomponent	340 years, rotor position sensor