

Right angle clevis foot LQG-100

Part number: 31773



Data sheet

Feature	Value
Size	100
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C...150 °C
Max. load capacity	9 kN
Product weight	1493 g
Note on materials	RoHS-compliant
Material mounting	Spheroidal graphite cast iron
Material bolt	Case-hardened steel
Material lock	Spring steel