

Sensorbox
SRBE-CA3-YR90-N-1-ZU-C2N12-C1
Part number: 3998922

FESTO



Data sheet

Feature	Value
Design	Angular
Based on standard	EN 60947-5-2 ISO 5211 VDI/VDE 3845
Approval	RCM trademark
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
Explosion protection	Class I, Div. 1 (CA) Class I, Div. 1 (US) Class I, Div. 2 (CA) Class I, Div. 2 (US) Class II, Div. 1 (CA) Class II, Div. 1 (US) Zone 1 (CA) Zone 1 (US) Zone 2 (CA) Zone 2 (US) Zone 21 (CA) Zone 21 (US)
Explosion ignition protection type for gas	AEx nA IIC T5 Gc Ex nA IIC T5 Gc
Explosion ignition protection type for dust	AEx tb IIIC T108°C Db Ex tb IIIC T108°C Db
Explosion protection certification outside the EU	Class I, Div. 1 (CA) Class I, Div. 1 (US) Class I, Div. 2 (CA) Class I, Div. 2 (US) Class II, Div. 1 (CA) Class II, Div. 1 (US) Class III (CA) Class III (US) EPL Db (CA) EPL Db (US) EPL Gb (CA) EPL Gb (US) EPL Gc (CA) EPL Gc (US)
Explosion ambient temperature	-20°C ≤ Ta ≤ +60°C
Certificate issuing authority	CSA 263311
Note on materials	RoHS-compliant

Feature	Value
Safety Integrity Level (SIL)	SIL 2
Measuring principle	Inductive
Ambient temperature	-20 °C...60 °C
Switching output	Non-contacting, 2-wire
Switching element function	N/O contact
Max. output current DC	4 mA...100 mA
Voltage drop	5 V
Min. load current	4 mA
Off-state current	0 mA...1 mA
Operational voltage range DC	5 V...60 V
Reverse polarity protection	For all electrical connections
Electrical connection	10-pin Screw terminal
Connectable nominal cross section conductor	0.25 mm²...2.5 mm²
Cable fitting	1/2 NPT
Type of mounting	On flange according to ISO 5211 Via mounting bracket
Connection point for positioner and position sensor conforms to standard	VDI/VDE 3845 size AA 1
Mounting position	optional
Product weight	1700 g
Housing colour	Silver
Material housing	Painted die cast aluminium
Material seals	NBR
Material shaft	High-alloy stainless steel
Material screws	High-alloy stainless steel
Material mounting bracket	High-alloy stainless steel
Material indicator	PC
Material snap ring	High-alloy stainless steel
Material disc	High-alloy stainless steel
Position indicator	Yellow/red
Setting range of angular detection	0 deg...90 deg
Storage temperature	-20 °C...60 °C
Degree of protection	IP67 NEMA 4/4X
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
LABS (PWIS) conformity	VDMA24364 zone III
Pollution degree	3