


Servo motor EMME-AS-80-MK-LS-AMX

Part number: 4267590

FESTO



Data sheet

Feature	Value
Ambient temperature	-10 °C...40 °C
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 90%
Conforms to standard	IEC 60034
Insulation protection class	F
Rating class as per EN 60034-1	S1
Degree of protection	IP21
Featherkey shaft type	DIN 6885 A 6 x 6 x 22
Electrical connector system	Plug
Note on materials	RoHS-compliant
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Approval	RCM trademark c UL us - Recognized (OL)
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK regulations for electrical equipment
Nominal operating voltage DC	360 V
Nominal voltage DC	360 V
Type of winding switch	Star inside
Number of pole pairs	3
Standstill torque	3.5 Nm
Nominal torque	3.2 Nm
Peak torque	14 Nm
Nominal rotary speed	3000 rpm
Max. rotational speed	4627 rpm
Nominal power rating of motor	1000 W
Continuous stall current	3.9 A
Nominal motor current	3.7 A

Feature	Value
Peak current	15.6 A
Motor constant	0.865 Nm/A
Voltage constant, phase-to-phase	55 mVmin
Phase-phase winding resistance	2.8 Ohm
Phase-phase winding inductance	7.43 mH
Total mass moment of inertia of output	1.93 kgcm ²
Product weight	3700 g
Permissible axial shaft load	72 N
Permissible radial shaft load	360 N
Rotor position sensor	Absolute multi-turn safety encoder
Rotor position encoder interface	HIPERFACE®
Rotor position sensor, encoder measuring principle	Optical
Rotor pos. enc., sin/cosin p/r	128
Rotor pos. encoder, typ. res.	15 bit
Rot. pos. enc., typ. ang. acc.	20 arcmin
Safety Integrity Level (SIL), subcomponent	SIL 2, rotor position sensor SILCL 2, rotor position sensor
Performance Level, subcomponent	Category 3, performance level d, rotor position encoder
PFHd, subcomponent	1.3 x 10E-8, rotor position sensor
Duration of use Tm, subcomponent	20 years, rotor position sensor
Mean time to dangerous failure (MTTFd), subcomponent	874 years, rotor position sensor
Energy efficiency	ENEFF (CN) / Class 2