

**Parallel kit**  
**EAMM-U-30-V20-28A-44**  
Part number: 4767125

**FESTO**



**Data sheet**

| Feature                               | Value                  |
|---------------------------------------|------------------------|
| Size                                  | 30                     |
| Centre-to-centre distance             | 44 mm                  |
| Mounting position                     | optional               |
| Gear unit ratio                       | 1:1                    |
| Max. rotational speed                 | 3000 rpm               |
| LABS (PWIS) conformity                | VDMA24364 zone III     |
| Storage temperature                   | -20 °C...60 °C         |
| Relative air humidity                 | 0 - 95%                |
| Degree of protection                  | IP40                   |
| Ambient temperature                   | 0 °C...50 °C           |
| Mass moment of inertia                | 2.11 kgmm <sup>2</sup> |
| Frictional torque independent of load | 0.015 Nm               |
| Transmittable torque                  | 0.05 Nm                |
| Product weight                        | 97 g                   |
| Interface code, actuator              | V20                    |
| Interface code, motor in              | 28A                    |
| Note on materials                     | RoHS-compliant         |