


Ball valve

VZBE-1/4-T-63-F-3T-F04-V15V15

Part number: 4834296

FESTO



Data sheet

Feature	Value
Design	3-way ball valve T-hole
Type of actuation	Mechanical
Sealing principle	Soft
Mounting position	optional
Type of mounting	In-line installation
Connection Process valve	1/4 NPT
Switching position indicator	Slot direction = flow direction
Flange hole pattern	F04
Inside diameter	11 mm
Nominal size DN	8
Valve function	3/2
Flow direction	Reversible
Nominal pressure PN	63
Breakaway torque at differential pressure, nominal pressure, process valve PN	9.6 Nm
Based on standard	ASME B1.20.1 ISO 5211
Medium	Vapour Compressed air to ISO 8573-1:2010 [:-:~] Inert gases Water Neutral fluids
Media temperature	-20 °C...200 °C
Flow rate Kv T hole angled	5 m³/h
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material housing	Stainless steel casting
Material number housing	1.4408
Material seat seal	PTFE

Feature	Value
Material seals	PTFE
Material ball	Stainless steel casting
Material number ball	1.4408
Material shaft	High-alloy stainless steel
Material number shaft	1.4401
Product weight	724 g
Approval	CRN
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class CRC	4 - Very high corrosion stress