



# Servo motor EMMT-AS-80-M-LS-RMB

Part number: 5255436

**FESTO**



## Data sheet

| Feature                                                   | Value                                                                                                                                                   |
|-----------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature                                       | -15 °C...40 °C                                                                                                                                          |
| Note on ambient temperature                               | Up to 80°C with derating of -1.5% per degree Celsius                                                                                                    |
| Max. installation height                                  | 4000 m                                                                                                                                                  |
| Note on max. installation height                          | As of 1,000 m: only with derating of -1.0% per 100 m                                                                                                    |
| Storage temperature                                       | -20 °C...70 °C                                                                                                                                          |
| Relative air humidity                                     | 0 - 90%                                                                                                                                                 |
| Conforms to standard                                      | IEC 60034                                                                                                                                               |
| Temperature class as per EN 60034-1                       | F                                                                                                                                                       |
| Max. winding temperature                                  | 155 °C                                                                                                                                                  |
| Rating class as per EN 60034-1                            | S1                                                                                                                                                      |
| Temperature monitoring                                    | Digital motor temperature transmission via EnDat® 2.2                                                                                                   |
| Motor type to EN 60034-7                                  | IM B5<br>IM V1<br>IM V3                                                                                                                                 |
| Mounting position                                         | optional                                                                                                                                                |
| Degree of protection                                      | IP40                                                                                                                                                    |
| Note on degree of protection                              | IP40 for motor shaft without rotary shaft seal<br>IP65 for motor shaft with rotary shaft seal<br>IP67 for motor housing including connection components |
| Concentricity, coaxiality, axial runout to DIN SPEC 42955 | N                                                                                                                                                       |
| Balance quality                                           | G 2.5                                                                                                                                                   |
| Detent torque                                             | <1.0% of peak torque                                                                                                                                    |
| Bearing lifetime under nominal conditions                 | 20000 h                                                                                                                                                 |
| Interface code, motor out                                 | 80P                                                                                                                                                     |
| Electrical connection 1, connection type                  | Hybrid plug                                                                                                                                             |
| Electrical connection 1, connector system                 | M23x1                                                                                                                                                   |
| Electrical connection 1, number of connections/cores      | 15                                                                                                                                                      |
| Pollution degree                                          | 2                                                                                                                                                       |
| Note on materials                                         | RoHS-compliant                                                                                                                                          |
| Corrosion resistance class CRC                            | 0 - No corrosion stress                                                                                                                                 |

| Feature                                                     | Value                                                                                               |
|-------------------------------------------------------------|-----------------------------------------------------------------------------------------------------|
| LABS (PWIS) conformity                                      | VDMA24364 zone III                                                                                  |
| Vibration resistance                                        | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6                    |
| Shock resistance                                            | Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27                                   |
| Approval                                                    | RCM trademark<br>c UL us - Recognized (OL)                                                          |
| CE mark (see declaration of conformity)                     | To EU EMC Directive<br>To EU Low Voltage Directive<br>In accordance with EU RoHS Directive          |
| UKCA marking (see declaration of conformity)                | To UK instructions for EMC<br>To UK RoHS instructions<br>To UK regulations for electrical equipment |
| Certificate issuing authority                               | UL E342973                                                                                          |
| Nominal operating voltage DC                                | 325 V                                                                                               |
| Type of winding switch                                      | Star inside                                                                                         |
| Number of pole pairs                                        | 5                                                                                                   |
| Standstill torque                                           | 2.6 Nm                                                                                              |
| Nominal torque                                              | 2.2 Nm                                                                                              |
| Peak torque                                                 | 6.4 Nm                                                                                              |
| Nominal rotary speed                                        | 3000 rpm                                                                                            |
| Max. rotational speed                                       | 6150 rpm                                                                                            |
| Max. mechanical speed                                       | 14000 rpm                                                                                           |
| Nominal power rating of motor                               | 690 W                                                                                               |
| Continuous stall current                                    | 4.9 A                                                                                               |
| Nominal motor current                                       | 4.1 A                                                                                               |
| Peak current                                                | 17.1 A                                                                                              |
| Motor constant                                              | 0.54 Nm/A                                                                                           |
| Standstill torque constant                                  | 0.62 Nm/A                                                                                           |
| Voltage constant, phase-to-phase                            | 37.3 mVmin                                                                                          |
| Phase-phase winding resistance                              | 2.04 Ohm                                                                                            |
| Phase-phase winding inductance                              | 8.9 mH                                                                                              |
| Winding longitudinal inductivity Ld (phase)                 | 5.4 mH                                                                                              |
| Winding cross inductivity Lq (phase)                        | 6.6 mH                                                                                              |
| Electric time constant                                      | 6.5 ms                                                                                              |
| Thermal time constant                                       | 45 min                                                                                              |
| Thermal resistance                                          | 0.78 K/W                                                                                            |
| Measuring flange                                            | 250 x 250 x 15 mm, steel                                                                            |
| Total mass moment of inertia of output                      | 1.285 kgcm <sup>2</sup>                                                                             |
| Product weight                                              | 3360 g                                                                                              |
| Permissible axial shaft load                                | 120 N                                                                                               |
| Permissible radial shaft load                               | 620 N                                                                                               |
| Rotor position sensor                                       | Absolute multi-turn encoder                                                                         |
| rotor position sensor, manufacturer designation             | EQI 1131                                                                                            |
| rotor position sensor, absolute detectable revolutions      | 4096                                                                                                |
| Rotor position encoder interface                            | EnDat® 22                                                                                           |
| Rotor position sensor, encoder measuring principle          | Inductive                                                                                           |
| rotor position sensor, DC operating voltage                 | 5 V                                                                                                 |
| rotor position sensor, DC operating voltage range           | 3.6 V...14 V                                                                                        |
| rotor position sensor, position values per revolution       | 524288                                                                                              |
| Rotor position transducer resolution                        | 19 bit                                                                                              |
| rotor position sensor, system accuracy of angle measurement | -120 arcsec...120 arcsec                                                                            |
| Brake holding torque                                        | 4.5 Nm                                                                                              |
| Operating voltage DC for brake                              | 24 V                                                                                                |
| Brake current consumption                                   | 0.5 A                                                                                               |

| Feature                                   | Value                                               |
|-------------------------------------------|-----------------------------------------------------|
| Power consumption, brake                  | 12 W                                                |
| Brake coil resistance                     | 48 Ohm                                              |
| Brake coil inductivity                    | 1000 mH                                             |
| Brake separation time                     | 55 ms                                               |
| Brake closing time                        | 15 ms                                               |
| DC brake response delay                   | 3 ms                                                |
| Max. brake no-load speed                  | 10000 rpm                                           |
| Max. friction per braking process         | 8200 J                                              |
| Mass moment of inertia of brake           | 0.249 kgcm <sup>2</sup>                             |
| Switching cycles holding brake            | 10 million idle actuations (without friction work!) |
| Mean time to failure (MTTF), subcomponent | 190 years, rotor position sensor                    |
| Energy efficiency                         | ENEFF (CN) / Class 2                                |