

Pressure gauge kit
DPA-100-10-MA-SET
Part number: 526098

FESTO



Data sheet

Feature	Value
Conforms to standard	EN 837-1
Nominal size of pressure gauge	40
Design	Bourdon tube pressure gauge
Type of mounting	Via male thread
Operating pressure	10 bar
Measurement accuracy class	2.5
Degree of protection	IP43
Ambient temperature	5 °C...60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Mounting position	optional
Pneumatic connection	G1/4
Product weight	305 g