

Compact cylinder DPDM-Q-16-5-S-PA

Part number: 4834367

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 5 mm |
| Piston diameter | 16 mm |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | optional |
| Mode of operation | Pushing Single-acting |
| Design | Piston Piston rod Profile barrel |
| Position detection | Via proximity switch |
| Variants | Piston rod at one end |
| Protection against torque/guide | Guide rod with yoke |
| Operating pressure | 0.2 MPa...0.8 MPa 2 bar...8 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 6 according to ISO 14644-1 |
| Ambient temperature | -10 °C...80 °C |
| Theoretical force at 0.6 MPa (6 bar, 87 psi) | 100 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 100 N |
| Moving mass for 0 mm stroke | 27 g |
| Additional moving mass per 10 mm stroke | 2.8 g |
| Basic weight for 0 mm stroke | 75 g |
| Additional weight per 10 mm stroke | 13.5 g |
| Type of mounting | Either: With through-hole Via female thread |
| Pneumatic connection | M5 |
| Note on materials | RoHS-compliant |
| Material cover | Wrought aluminium alloy |

| Feature | Value |
|---------------------|----------------------------------|
| Material seals | NBR TPE-U(PU) |
| Material housing | Anodised wrought aluminium alloy |
| Material piston rod | High-alloy stainless steel |