



# Service unit combination

## MSB4-1/4:H1N2M1-WP

Part number: 531085

FESTO

Comprising filter, pressure regulator, lubricator, wall mounting plate.  
Maximum output pressure 7 bar, 40 µm filter, with pressure gauge,  
plastic bowl with plastic bowl guard, fully automatic condensate drain,  
flow direction from left to right.



## Data sheet

Feature	Value
Size	4
Series	MS
Assembly position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	fully automatic
Design structure	Pressure regulator with gauge Standard filter Standard oil-mist lubricator
Bowl guard	Plastic guard
Pressure gauge	with pressure gauge
Operating pressure	2 ... 12 bar
Pressure control range	1 ... 7 bar
Standard nominal flow rate	1,300 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:-] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Storage temperature	-10 ... 60 °C
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [7:4:-]
Medium temperature	-10 ... 60 °C
Product weight	1,000 g
Mounting type	with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4