


Activated carbon filter MS6N-LFX-3/8-U

Part number: 531928

FESTO



Data sheet

Feature	Value
Size	6
Series	MS
Mounting position	Vertical +/-5°
Design	Activated carbon filter
Bowl guard	Integrated as metal bowl
Operating pressure	0 bar...20 bar
Max. standard flow rate for clean air class	900 l/min
Operating medium	Druckluft nach ISO 8573-1:2010 [3:4:2]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Suitable for use with food	See supplementary material information
Air purity class at output	Druckluft nach ISO 8573-1:2010 [3:4:1]
Media temperature	5 °C...30 °C
Residual oil content	0.003 mg/m³
Ambient temperature	-10 °C...60 °C
Product weight	820 g
Type of mounting	In-line installation With accessories Either:
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	G3/8
Note on materials	RoHS-compliant
Material filter	Activated carbon
Material housing	Die-cast aluminium
Material bowl	Wrought aluminium alloy