



# Service unit combination MSB4-1/4:H3N3M1-WP-Z

Part number: 531098

FESTO

Consisting of filter, pressure regulator, lubricator and wall mounting plate. 12 bar maximum output pressure, 5 µm filter, with pressure gauge, plastic bowl with plastic bowl guard, manual condensate drain, direction of flow: from right to left.



## Data sheet

Feature	Value
Size	4
Series	MS
Actuator lock	Rotary knob with lock with accessories, lockable
Assembly position	Vertical +/- 5°
Grade of filtration	5 µm
Condensate drain	manual rotary
Design structure	Pressure regulator with gauge Standard filter Standard oil-mist lubricator
Bowl guard	Plastic guard
Pressure gauge	with pressure gauge
Pressure control range	1 ... 12 bar
Inlet pressure 1	1.5 ... 14 bar
Standard nominal flow rate	700 l/min
Operating medium	Filtered, unlubricated compressed air, 40 µm filtration Filtered, lubricated compressed air, 40 µm filtration
Corrosion resistance classification CRC	2
Storage temperature	-10 ... 60 °C
Air purity class at output	3.7.- per DIN ISO 8573-1
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	1,000 g
Mounting type	with accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Materials information, housing	Aluminium die cast
Materials information for bowl	PC