

Filter
MS12N-LF
Part number: 535026

FESTO



Data sheet

Feature	Value
Size	12
Series	MS
Mounting position	Vertical +/-5°
Condensate drain	Fully automatic Fully automatic, electrically actuated Manual, non-detenting Manually rotating
Design	Sintered filter with centrifugal separator
Degree of condensate separation	75 %
Operating pressure	0.8 bar...20 bar
Operating medium	Compressed air to ISO 8573-1:2010 [-:9:-] Compressed air to ISO 8573-1:2010 [7:9:-] Inert gases
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Type of mounting	Either: In-line installation With accessories
Pneumatic connection, port 1	Internal
Pneumatic connection, port 2	Internal
Material housing	Die-cast aluminium
Material bowl	Wrought aluminium alloy