

Lubricator
MS12-LOE
Part number: 535041

FESTO



Data sheet

Feature	Value
Size	12
Series	MS
Mounting position	Vertical +/-5°
Design	Proportional standard mist lubricator
Operating pressure	1 bar...16 bar
Min. flow rate for lubricator function	400 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [:-:-]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Oil viscosity	ISO VG 32
Ambient temperature	0 °C...60 °C
Type of mounting	In-line installation With accessories Either:
Material housing	Die-cast aluminium
Material bowl	Wrought aluminium alloy