



# distance sensor SOEG-RTD-Q20-PP-K-2L-TI

Part number: 537758  
Product to be discontinued

FESTO

[For distance measurement, block design](#)

Type to be discontinued. Available until 2020. See Support Portal for alternative products.



## Data sheet

Feature	Value
Design	Block design
Authorisation	RCM Mark c UL us - Listed (OL)
CE mark (see declaration of conformity)	to EU directive for EMC
Materials note	Free of copper and PTFE
Measured variable	Travel
Measuring principle	Optoelectronic
Measurement method	Distance sensor
Type of light	Red
Max. spot diameter	5 x 5 mm with a sensing range of 60 mm
Working range	20 ... 80 mm
Ambient temperature	0 ... 60 °C
Travel resolution	0.5 mm
Switch output	PNP
Switching element function	Switchable
Max. switching frequency	200 Hz
Max. output current	100 mA
Voltage drop	≤ 2.4 V
Analogue output	0 - 10 V
Short circuit strength	Pulsing
Operating voltage range DC	15 ... 30 V
Residual ripple	10 %
Idle current	25 mA
Polarity protected	for all electrical connections
Electrical connection	Cable 4-core
Cable length	2 m
Material cable sheath	TPE-U(PUR)
Size	20x32x12 mm
Mounting type	with through hole
Product weight	37 g
Material housing	ABS
Operating status display	Yellow LED
Operating reserve display	Green LED
Setting options	Teach-In Teach-in via electrical connection
Setting range lower limit	20 mm
Upper limit of adjustment range	80 mm
Ambient temperature with flexible cable installation	0 ... 60 °C
Protection class	IP67
Corrosion resistance classification CRC	4 - Very high corrosion stress