

# Condensate drain PWEA-AP-3D

Part number: 538678

FESTO

For external attachment, with independent electrical controller.



## Data sheet

Feature	Value
Type of actuation	electrical
Assembly position	Vertical +/- 5°
Manual override	Pushing
Condensate drain	fully automatic
Design structure	External, electrical, fully automated
Measured variable	Fill-level
Valve function	closed 3/2 monostable
Control elements	Membrane keypad With test key
Ready status display	LED
Operating status display	LED
Operating pressure	0.8 ... 16 bar
Alarm output	Contact-type
Nominal operating voltage DC	24 V
Nominal capacity, condensate drain	2 W
Operating medium	Compressed air
Corrosion resistance classification CRC	2
Storage temperature	-10 ... 60 °C
Medium temperature	1 ... 60 °C
Protection class	IP65 to IEC 60529
Safety class	III
Ambient temperature	1 ... 60 °C
Product weight	700 g
Electrical connection	Plug M12x1 5-pin Round design
Mounting type	Line installation
Condensate drain connection	PK-8
Pneumatic connection	G1/2
Material information, condensate container	Wrought Aluminium alloy
Materials note	Free of copper and PTFE
Materials information, housing	Plastic