


# Pick&Place DHSP-HSP25

Part number: 543049

FESTO

Mechanism guided by connecting link, electric or pneumatic drive for two directions of motion, compact and very dynamic. Defined interfaces to Festo's rotary and gripper range. Order as a mounting kit or completely assembled and installed.

Please click above on symbol FAX request, to obtain a non-binding offer to fulfil your requirements.



## Data sheet

Feature	Value
Assembly	Pick&Place 1.0
Effective load	0 ... 1.6 kg
Drive system, Z axis	Pneumatic
Stroke, Z axis	20 ... 70 mm
Repetition accuracy in the end position, Z axis	± 0,02 mm
Repetition accuracy in the intermediate position, Z axis	± 0,02 mm
Drive unit, Y axis	HSP-25
Drive system, Y axis	Pneumatic
Stroke, Y axis	52 ... 170 mm
Repetition accuracy in the end position, Y axis	± 0,02 mm
Repetition accuracy in the intermediate position, Y axis	± 0,02 mm