


Proximity sensor SIEF-M8B-NS-S-L

Part number: 553539

FESTO



Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Approval	RCM trademark c UL us listed (OL)
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK regulations for electrical equipment
Note on materials	RoHS-compliant
Rated operating distance	1.5 mm
Ambient temperature	-30 °C...85 °C
Repetition accuracy	0.08 mm
Switching output	NPN
Switching element function	N/O contact
Max. switching frequency DC	2000 Hz
Max. output current	150 mA
Short circuit current rating	Pulsed
Operational voltage range DC	10 V...30 V
Reverse polarity protection	For all electrical connections
Electrical connection	3-pin M8x1 Plugs
Material connector housing	Brass Chrome-plated
Size	M8
Mounting type	Flush
Product weight	12 g
Material housing	PA High-alloy stainless steel
Switching status indication	Yellow LED
Degree of protection	IP68
Immunity to magnetic fields	Magnetic direct and alternating field

Feature	Value
Immunity to surge	0.8 kV
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Pollution degree	3
Additional information for sensor selection	Reduction factor 1, resistant to magnetic fields
Selection of sensor design	Standard