


Fine filter
MS9-LFM-1-BUM-HF
Part number: 553042

FESTO



Data sheet

Feature	Value
Series	MS
Size	9
Design	Fibre filter
Grade of filtration	1 µm
Condensate drain	Manually rotating
Operating pressure	0 MPa...2 MPa 0 bar...20 bar 0 psi...290 psi
Operating medium	Compressed air to ISO 8573-1:2010 [6:-:4]
Air purity class at output	Compressed air to ISO 8573-1:2010[5:-:3]
Max. standard flow rate for clean air class	10000 l/min
Min. standard flow rate for clean air class	500 l/min
Filter efficiency	99.99 %
Max. condensate volume	225 ml
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Storage temperature	-10 °C...60 °C
Filter efficiency, fine particles	99 %
Residual oil content	0.5 mg/m ³
Filter efficiency, oil aerosol	90 %
Explosion ambient temperature	-10 °C ≤ Ta ≤ +60 °C
Type of mounting	Either: In-line installation With accessories
Mounting position	Vertical +/-5°
Pneumatic connection, port 1	G1
Pneumatic connection, port 2	G1
Material housing	Die-cast aluminium
Material covering	PA
Material filter	Borosilicate fibre

Feature	Value
Material bowl	Wrought aluminium alloy
Material screen	PA
Material seals	NBR
Product weight	2500 g