

Ball screw axis EGC-70- -BS-KF

Part number: 556807

FESTO



Data sheet

Feature	Value
Working stroke	50 mm...1000 mm
Size	70
Spindle diameter	12 mm
Spindle pitch	10 mm/U
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Electromechanical linear axis With ball screw
Type of motor	Stepper motor Servo motor
Spindle type	Ball screw
Functional principle of measuring system	Incremental
Max. acceleration	15 m/s ²
Max. speed	0.5 m/s
Repetition accuracy	±0.02 mm
Duty cycle	100%
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
2nd moment of area I _y	419000 mm ⁴
2nd moment of area I _z	578000 mm ⁴
Max. force F _y	1850 N
Max. force F _z	1850 N
Max. force F _y total axis	1850 N
Max. force F _z total axis	1850 N
F _y at theoretical life value of 100 km (only guide consideration)	6815 N
F _z at theoretical life value of 100 km (only guide consideration)	6815 N
Max. moment M _x	16 Nm
Max. moment M _y	51 Nm...132 Nm
Max. moment M _z	51 Nm...132 Nm
Max. moment M _x total axis	16 Nm
Max. moment M _y total axis	51 Nm...132 Nm

Feature	Value
Max. moment Mz total axis	51 Nm...132 Nm
Mx at theoretical life value of 100 km (only guide consideration)	59 Nm
My at theoretical life value of 100 km (only guide consideration)	188 Nm...486 Nm
Mz at theoretical life value of 100 km (only guide consideration)	188 Nm...486 Nm
Max. radial force at drive shaft	220 N
Max. feed force Fx	400 N
Torsional mass moment of inertia It	88000 mm ⁴
Mass moment of inertia JH per metre of stroke	0.142 kgcm ²
Feed constant	10 mm/U
Reference service life	5000 km
Material end cap	Wrought aluminium alloy Anodised
Material driver	Wrought aluminium alloy Anodised
Material profile	Wrought aluminium alloy Anodised
Note on materials	RoHS-compliant
Material drive cover	Wrought aluminium alloy Anodised
Material guide slide	Steel
Material guide rail	Steel
Material slide	Wrought aluminium alloy Anodised
Material spindle nut	Steel
Material spindle	Steel