


Motor flange
EAMF-A-38A-70A
Part number: 558018

FESTO



Data sheet

Feature	Value
Mounting position	optional
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-10 °C...60 °C
Product weight	158 g
Interface code, motor in	70A
Interface code, clutch housing	38A
Note on materials	RoHS-compliant