



Solenoid valve

VOVG-B12-M52Q-AH-F-1H2

Part number: 560713

FESTO



Data sheet

Feature	Value
Valve function	5/2-way, monostable
Type of actuation	Electric
Construction width	25 mm
Standard nominal flow rate (standardised to DIN 1343)	180 l/min
pneumatic working port	Sub-base
Operating voltage	24V DC
Operating pressure	0.2 MPa...0.8 MPa 2 bar...8 bar 29 psi...116 psi
Design	Piston gate valve
Type of reset	Pneumatic spring
Degree of protection	IP40
Nominal size	2.1 mm
Exhaust-air function	With flow control option
Sealing principle	Soft
Mounting position	optional
Manual override	Non-detenting
Type of piloting	Pilot actuated
Flow direction	Non-reversible
lap	Overlap
Switching time off	18 ms
Switching time on	15 ms
Characteristic coil data	24 V DC: 1.0 W
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Media temperature	-5 °C...50 °C
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Ambient temperature	-5 °C...50 °C

Feature	Value
Electrical connection	2-pin Plugs
Pneumatic connection, port 1	Sub-base
Pneumatic connection, port 2	Sub-base
Pneumatic connection, port 3	Sub-base
Note on materials	RoHS-compliant
Material seals	FPM HNBR NBR
Material housing	Wrought aluminium alloy