


Axial kit
EAMM-A-L27-40G
Part number: 557974



Data sheet

Feature	Value
Nominal length	28.7 mm
Mounting position	optional
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	0.445 kgmm ²
Transmittable torque	2 Nm
Product weight	180 g
Interface code, actuator	L27
Interface code, motor in	40G
Note on materials	RoHS-compliant