

Coupling
EAMD-56-46-19-23X27
Part number: 558003

FESTO



Data sheet

Feature	Value
Mounting diameter 1	19 mm
Mounting diameter 2	23 mm
Size	56
Nominal length	46.5 mm
Mounting position	optional
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	151 kgmm ²
Transmittable torque	60 Nm
Product weight	418 g
Note on materials	RoHS-compliant