

Electrical slide EGSK-26-150-2P

Part number: 562766

FESTO



Data sheet

Feature	Value
Working stroke	150 mm
Size	26
Reversing backlash theoretical	20 µm
Spindle diameter	8 mm
Spindle pitch	2 mm/U
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Electromechanical linear axis With ball screw drive
Referencing	Reference switch
Spindle type	Ball screw drive
Max. acceleration	10 m/s ²
Max. speed	0.28 m/s
Repetition accuracy	±0.01 mm
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP10
Ambient temperature	0 °C...40 °C
Dynamic basic load rating fixed bearing	1380 N
Dynamic basic load rating linear guide	5746 N
Dynamic basic load rating ball screw	2350 N
2nd moment of area I _y	17000 mm ⁴
2nd moment of area I _z	150000 mm ⁴
Max. drive torque	0.037 Nm
Max. force F _y	2223 N
Max. force F _z	2223 N
Max. moment M _x	37.8 Nm
Max. moment M _y	12.9 Nm
Max. moment M _z	12.9 Nm
Max. feed force F _x	116 N
Frictional torque independent of load	0.015 Nm
Static basic load rating ball screw	4020 N

Feature	Value
Static basic load rating linear guide	12150 N
Mass moment of inertia JH per metre of stroke	0.0316 kgcm ²
Mass moment of inertia JO	0.00357 kgcm ²
Feed constant	2 mm/U
Static basic load rating fixed bearing	1760 N
Reference service life	1000 km
Moving mass	153 g
Weight of slide	153 g
Product weight	1410 g
Weight of additional slide	153 g
Basic weight for 0 mm stroke	780 g
Additional weight per 10 mm stroke	42 g
Type of mounting	Via female thread and dowel pin
Material end cap	Die-cast aluminium Coated
Material profile	High-alloy stainless steel
Note on materials	RoHS-compliant
Material drive cover	Die-cast aluminium Coated
Material slide	Steel
Material spindle nut	Steel
Material spindle	Steel