


Water separator MS9-LWS

Part number: 567857

FESTO



Data sheet

Feature	Value
Size	9
Series	MS
Mounting position	Vertical +/-5°
Condensate drain	Fully automatic Fully automatic, electrically actuated Manual, non-detenting
Design	Centrifugal separator
Max. condensate volume	220 ml
Bowl guard	Integrated as metal bowl
Degree of condensate separation	99 %
Operating pressure	0.8 bar...16 bar
Standard nominal flow rate (standardised to DIN 1343)	12000 l/min...15000 l/min
Approval	c UL us - Recognized (OL)
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity)	To UK EX instructions
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)
Explosion protection	Zone 1 (ATEX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 21 (UKEX) Zone 22 (ATEX)
ATEX category gas	II 2G
ATEX category dust	II 2D
Explosion ignition protection type for gas	Ex h IIC T6 Gb X
Explosion ignition protection type for dust	Ex h IIIC T60°C Db X
Explosion ambient temperature	+5°C ≤ Ta ≤ +60°C
Operating medium	Compressed air to ISO 8573-1:2010 [-:7:4]
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	1 °C...60 °C

Feature	Value
Air purity class at output	Compressed air to ISO 8573-1:2010 [-:7:4]
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	2000 g
Type of mounting	In-line installation With accessories Either:
Material covering	PA-reinforced
Material spin disc	POM
Note on materials	RoHS-compliant
Material sub-base	Die-cast aluminium
Material mounting bracket	Die-cast aluminium
Material housing	Die-cast aluminium
Material module connector	Die-cast aluminium
Material bowl	Wrought aluminium alloy
Material cup seal	NBR
Material screen	PA
Material separating plate	POM