


Toothed belt axis ELGG-TB-...-45- -

Part number: 571059

FESTO



Data sheet

Feature	Value
Effective diameter of drive pinion	24.83 mm
Working stroke	50 mm...900 mm
Size	45
Toothed-belt stretch	0.08 %
Toothed-belt pitch	3 mm
Mounting position	optional
Guide	Plain-bearing guide Recirculating ball bearing guide
Design	Electromechanical linear axis With toothed belt
Type of motor	Stepper motor Servo motor
Max. acceleration	50 m/s ²
Max. speed	1 m/s...3 m/s
Repetition accuracy	±0.1 mm
Duty cycle	100%
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP20
Ambient temperature	-10 °C...50 °C
2nd moment of area I _y	15700 mm ⁴
2nd moment of area I _z	17940 mm ⁴
Max. drive torque	1.24 Nm
Max. force F _y	100 N
Max. force F _z	100 N
Max. idle running transfer resistance	16.1 N
Max. feed force F _x	100 N
Frictional torque independent of load	0.2 Nm
Mass moment of inertia J _H per metre of stroke	0.011 kgcm ²
Mass moment of inertia J _L per kg of working load	1.54 kgcm ²
Feed constant	78 mm/U
Reference service life	2500 km
Additional moving mass per 10 mm stroke	0.69 g

Feature	Value
Basic weight for 0 mm stroke	4230 g
Additional weight per 10 mm stroke	100 g
Material profile	Wrought aluminium alloy Anodised
Note on materials	RoHS-compliant
Material drive cover	Wrought aluminium alloy Anodised
Material pulleys	High-alloy stainless steel
Material slide	Wrought aluminium alloy Anodised
Material toothed belt clamping piece	Beryllium bronze
Material toothed belt	Polychloroprene oder Nitrilkautschuk (NBR) mit Glascord und Nylonüberzug