



Water separator MS9-LWS-G-U-V

Part number: 571468

FESTO



Data sheet

Feature	Value
Size	9
Series	MS
Mounting position	Vertical +/-5°
Condensate drain	Fully automatic
Design	Centrifugal separator
Max. condensate volume	220 ml
Bowl guard	Integrated as metal bowl
Degree of condensate separation	99 %
Operating pressure	2 bar...12 bar
Standard nominal flow rate (standardised to DIN 1343)	15000 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [-:7:4]
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	5 °C...60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [-:7:4]
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	2000 g
Type of mounting	In-line installation With accessories Either:
Material covering	PA-reinforced
Material spin disc	POM
Note on materials	RoHS-compliant
Material sub-base	Die-cast aluminium
Material mounting bracket	Die-cast aluminium
Material housing	Die-cast aluminium
Material module connector	Die-cast aluminium
Material bowl	Wrought aluminium alloy
Material cup seal	NBR

Feature	Value
Material screen	PA
Material separating plate	POM