

Input module

CPX-L-16DE-16-KL-3POL

Part number: 572606

FESTO



Data sheet

Feature	Value
Dimensions (W x L x H)	(incl. interlinking block) 50 x 107 x 41 mm
Product weight	167 g
Ambient temperature	-5 °C...50 °C
Storage temperature	-20 °C...70 °C
Degree of protection	IP20
Corrosion resistance class CRC	1 - Low corrosion stress (when installed)
LABS (PWIS) conformity	VDMA24364-B2-L
Approval	c UL us listed (OL)
Note on materials	RoHS-compliant
Material housing	PA-reinforced
LED display	1 Group diagnostics 16 Channel status
Diagnosis	Short circuit/overload per channel
Parameterisation	Input debounce time Signal extension time Behaviour after short circuit Module monitoring
Operational voltage range DC	18 V...30 V
Nominal operating voltage DC	24 V
Intern power consumption nominal operating voltage	Typ. 15 mA
Number of inputs	16
Characteristic for inputs	IEC1131-T2, type 01
Switching level	Signal 0: <= 5 V Signal 1: >= 15 V
Switching logic for inputs	PNP (positive switching)
Input debounce time	3 ms (0.1 ms, 10 ms, 20 ms, parameterisable)
Max. residual current of inputs per module	1.8 A
Isolation channel - channel	no
Isolation channel - internal bus	no
Fuse protection (short circuit)	Internal electronic fuse per module