



Distributor
NEDY-L2R1-V1-A1W4L-U-0.3L-M8G4-2.5R
Part number: 8035793

FESTO



Data sheet

Feature	Value
Based on standard	EN 175301-803 EN 61076-2-104
Design	Y-distributor with cables on both sides
Distribution	Y type
Signal status display	Yellow LED
Cable designation	With label holder
Type of mounting	Via through-hole for M2 screw With accessories
Product weight	117 g
Electrical connection 1, function	Controller side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Plugs
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	M8x1, A-coded, to EN 61076-2-104
Electrical connection 1, number of connections/cores	4
Electrical connection 1, used connections/cores	3
Electrical connection 2, function	Field device side
Electrical connection 2, design	Angular
Electrical connection 2, connection type	2x socket
Electrical connection 2, cable outlet	Angled
Electrical connection 2, connector system	Plug pattern type A to EN 175301-803
Electrical connection 2, number of connections/cores	4
Electrical connection 2, used connections/cores	2
Operational voltage range DC	20.4 V...27.6 V
Current rating at 40° C	3 A
Immunity to surge	0.8 kV
Cable length 1	2.5 m
Cable length 2	0.3 m
Cable characteristic	Suitable for energy chains/robot applications

Feature	Value
Test conditions cable	Bending strength: to Festo standard Test conditions on request Torsionsfestigkeit: > 300 000 Zyklen, ±270°/0,1 m Energy chain: > 5 million cycles, bending radius 28 mm
Min. bending radius with free moving insert 1	39 mm
Min. bending radius with free moving insert 2	39 mm
Cable diameter 1	3.8 mm
Cable diameter 2	3.8 mm
Nominal cross section conductor	0.25 mm ²
Degree of protection	IP65 IP67
Ambient temperature	-20 °C...80 °C
Note on ambient temperature	-10 - 40°C with mounting via through-hole
Ambient temperature with moving cable	-20 °C...80 °C
Storage temperature	-20 °C...80 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
CE marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant Free of halogen Free of phosphoric acid ester
Pollution degree	3
Corrosion resistance class CRC	1 - Low corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath colour	Grey
Material housing	PA PC TPE-U(PUR)
Housing colour	Black
Material seals	NBR
Material electrical contact	Gold-plated copper alloy Silver-plated copper alloy
Material threaded sleeve	Nickel-plated brass