

Sub-base VABS-P12-S-M5-P3

Part number: 8068637

FESTO



Data sheet

Feature	Value
Construction width	25 mm
Mounting position	optional
Special characteristics	Oxygen-compatible to DIN EN 1797
Max. number of valve positions	1
Operating pressure	0 bar...1.7 bar
Standard nominal flow rate (standardised to DIN 1343)	27 l/min
Standard nominal flow rate 2-3	28 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [5:3:1] Inert gases Oxygen
Note on operating and pilot medium	Lubricated operation not possible Maximum particle size 5 µm
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C...70 °C
Media temperature	-20 °C...60 °C
Relative air humidity	0 - 70 % Non-condensing
Degree of protection	IP00
Note on degree of protection	In assembled state
Ambient temperature	-20 °C...70 °C
Product weight	55 g
Type of mounting	With through-hole
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M5
Pneumatic connection, port 2S	M5
Pneumatic connection, port 3	M5
Pneumatic connection, port 5	M5
Note on materials	RoHS-compliant
Material sub-base	Anodised wrought aluminium alloy