


Ball screw axis ELGC-BS-KF-45-800-10P

Part number: 8061490

FESTO



Data sheet

Feature	Value
Working stroke	800 mm
Size	45
Stroke reserve	0 mm
Reversing backlash theoretical	0.15 mm
Spindle diameter	10 mm
Spindle pitch	10 mm/U
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Electromechanical linear axis With ball screw
Type of motor	Stepper motor Servo motor
Spindle type	Ball screw drive
Position detection	Via proximity switch Via inductive sensors
Max. acceleration	15 m/s ²
Max. rotational speed	3600 rpm
Max. speed	0.6 m/s
Repetition accuracy	±0.015 mm
Duty cycle	100%
LABS (PWIS) conformity	VDMA24364 zone III
Suitability for the production of Li-ion batteries	Product corresponds to the internal product definition from Festo for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 7 according to ISO 14644-1
Storage temperature	-20 °C...60 °C
Degree of protection	IP40
Ambient temperature	0 °C...50 °C
Impact energy in end positions	0.5 mJ
Note on the impact energy in the end positions	At maximum homing speed of 0.01 m/s
2nd moment of area Iy	140000 mm ⁴

Feature	Value
2nd moment of area Iz	170000 mm ⁴
Idle torque at v _{max}	0.12 Nm
Idle torque at v _{min}	0.032 Nm
Max. force F _y	880 N
Max. force F _z	880 N
Max. force F _y total axis	300 N
Max. force F _z total axis	600 N
F _y at theoretical life value of 100 km (only guide consideration)	3240 N
F _z at theoretical life value of 100 km (only guide consideration)	3240 N
Max. moment M _x	5.5 Nm
Max. moment M _y	4.7 Nm
Max. moment M _z	4.7 Nm
Max. moment M _x total axis	5.5 Nm
Max. moment M _y total axis	4.7 Nm
Max. moment M _z total axis	4.7 Nm
M _x at theoretical life value of 100 km (only guide consideration)	20 Nm
M _y at theoretical life value of 100 km (only guide consideration)	17 Nm
M _z at theoretical life value of 100 km (only guide consideration)	17 Nm
Distance between slide surface and guide centre	42.8 mm
Max. radial force at drive shaft	180 N
Max. feed force F _x	100 N
Torsional mass moment of inertia I _t	8500 mm ⁴
Mass moment of inertia J _H per metre of stroke	0.05056 kgcm ²
Mass moment of inertia J _L per kg of working load	0.02533 kgcm ²
Mass moment of inertia J _O	0.0082 kgcm ²
Feed constant	10 mm/U
Reference service life	5000 km
Maintenance interval	Life-time lubrication
Moving mass	220 g
Additional weight per 10 mm stroke	36 g
Dynamic deflection (moving load)	0.05% of the axis length, max. 0.5 mm
Static deflection (load in standstill)	0.1% of the axis length
Interface code, actuator	V32
Material end cap	Painted die cast aluminium
Material profile	Anodised wrought aluminium alloy
Note on materials	RoHS-compliant
Material cover tape	High-alloy stainless steel
Material drive cover	Painted die cast aluminium
Material guide slide	Steel
Material guide rail	Steel
Material slide	Die-cast aluminium
Material spindle nut	Steel
Material spindle	Steel