

# Proportional-pressure regulator VPPI-

Part number: 8074287

**FESTO**



## Data sheet

Feature	Value
Nominal size, supply	5 mm
Nominal size, exhaust	5 mm
Type of actuation	Electric
Sealing principle	Soft
Total leakage	5 l/h
Flow direction	Non-reversible
Mounting position	optional
Design	Poppet valve with spring return
Short circuit current rating	For all electrical connections
Max. cable length	30 m
Setpoint value input	0 - 10 V 4 - 20 mA PWM Digital
Input resistance	0.3 kOhm...100 kOhm
Safety instructions	Safety position VPPI, normally closed Safety position VPPI, normally open
Reverse polarity protection	For all electrical connections
Type of reset	Mechanical spring
Dimensions (W x L x H)	42.2 x 95.3 x 94.3 mm
Type of piloting	Direct
Valve function	3-way proportional pressure regulator
Display type	LED TFT colour
Display size	1.77"
Display resolution	128x160 pixels
Operating pressure	0 bar...13 bar
Pressure regulation range	-0.1 MPa...1.2 MPa -1 bar...12 bar
Inlet pressure 1	0 bar...13 bar 0 MPa...1.3 MPa
Input pressure 3	-0.1 MPa...0 MPa -1 bar...0 bar

Feature	Value
Burst pressure	40 bar 725 psi
Standard nominal flow rate (standardised to DIN 1343)	150 l/min...1630 l/min
Standard nominal flow rate 2-3	20 l/min...850 l/min
Operational voltage range DC	21.6 V...27.6 V
Nominal operating voltage DC	24 V
Switching output	Push-pull
Max. output current	25 mA
Signal range analogue output	0 - 10 V 4 - 20 mA
Max. load resistance current output	500 Ohm
Min. load resistance voltage output	2000 Ohm
Accuracy analogue output in $\pm$ %FS	1 %FS
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation not possible
Approval	FCC MIC RCM trademark c UL us listed (OL)
KC mark	KC-EMV
CE mark (see declaration of conformity)	To EU EMC Directive EU-radio equipment-directive (RED) In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 4 according to ISO 14644-1
Suitable for use with food	See supplementary material information
Media temperature	0 °C...50 °C
Degree of protection	IP65
Ambient temperature	0 °C...50 °C
Storage temperature	-20 °C...70 °C
Climatic category	3K3 as per EN 60721
Relative air humidity	0 - 85% Non-condensing
Nominal altitude of use	< 3000 m NHN
Instructions on use	The product is suitable for industrial purposes only. Measures to eliminate radio interference may be required in residential areas.
Sound power level	62.5 dB(A)
Sound power level at a distance of 1 m	51.9 dB(A)
Product weight	365 g...370 g
Linearity	0.9 %FS
Hysteresis	0.4 %FS
Reproducibility	0.4 %FS
Electrical connection 1, function	Actual value output Setpoint input Power supply
Electrical connection 1, connection type	Plugs
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 1, number of connections/cores	5
Electrical connection 1, tightening torque	1.5 Nm

Feature	Value
Type of mounting	Via through-hole for M4 screw With H-rail
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Pneumatic connection, port 3	G1/8
Max. tightening torque for fitting	8.5 Nm
Note on materials	RoHS-compliant
Material housing	PA-reinforced
Material seals	HNBR PTFE