


Mini slide DGST-10-50-Y12A

Part number: 8085168

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 50 mm |
| Adjustable end position range/length front | 16.2 mm |
| Adjustable end position range/length rear | 14.5 mm |
| Piston diameter | 10 mm |
| Operating mode, drive unit | Yoke |
| Cushioning | External hydraulic cushioning |
| Mounting position | optional |
| Guide | Recirculating ball bearing guide |
| Design | Twin piston Yoke Piston rod Slide |
| Position detection | Via proximity switch |
| Operating pressure | 0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi |
| Max. speed | 0.8 m/s |
| Repetition accuracy | <= 0.02 mm |
| Mode of operation | Double-acting |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom class | Class 6 according to ISO 14644-1 |
| Ambient temperature | -10 °C...60 °C |
| Impact energy in end positions | 0.8 J |
| Cushioning length | 4 mm |
| Max. force F _y | 510 N |
| Max. force F _z | 510 N |
| Max. moment M _x | 5 Nm |
| Max. moment M _y | 4.5 Nm |

| Feature | Value |
|--|----------------------------------|
| Max. moment Mz | 4.5 Nm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 79 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 94 N |
| Moving mass | 187.2 g |
| Product weight | 379.4 g |
| Type of mounting | With through-hole |
| Pneumatic connection | M5 |
| Note on materials | RoHS-compliant |
| Material cover | Wrought aluminium alloy |
| Material seals | HNBR |
| Material guide | POM TPE-E High-alloy steel |
| Material housing | Wrought aluminium alloy |
| Material piston rod | High-alloy stainless steel |