

Servo Press Kit YJKP

Part number: 8077950

FESTO



Data sheet

Feature	Value
Pressing force	0 kN...17 kN
Working stroke	100 mm...400 mm
Cable length	5 m...15 m
Scanning frequency	1000 Hz
Protocol	EtherNet/IP Modbus® TCP OPC UA PROFINET IO TCP/IP
Mounting position	optional
Type of motor	Servo motor
Max. acceleration	2 m/s ²
Duty cycle	100%
Feed speed	0 mm/s...250 mm/s
Accuracy in ± % FS	0.25 %FS
Max. effective load	19.5 kg...95 kg
Product weight	5.5 kg...66.7 kg
Ambient temperature	0 °C...40 °C
Storage temperature	-10 °C...60 °C
Degree of protection	IP20
Relative air humidity	0 - 90%
Note on materials	RoHS-compliant
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III