

Mini slide DGST-6-40-E1A

Part number: 8078831

FESTO



Data sheet

Feature	Value
Stroke	40 mm
Piston diameter	6 mm
Operating mode, drive unit	Yoke
Cushioning	Elastomer cushioning, double-sided, stroke not adjustable
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Twin piston Yoke Piston rod Slide
Position detection	Via proximity switch
Operating pressure	0.15 MPa...0.8 MPa 1.5 bar...8 bar 21.75 psi...116 psi
Max. speed	0.5 m/s
Repetition accuracy	<= 0.3 mm
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...60 °C
Impact energy in end positions	0.012 J
Cushioning length	0.9 mm
Max. force Fy	260 N
Max. force Fz	260 N
Max. moment Mx	1.2 Nm
Max. moment My	1.2 Nm
Max. moment Mz	1.2 Nm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	25 N

Feature	Value
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	34 N
Moving mass	73 g
Product weight	140 g
Type of mounting	With through-hole
Pneumatic connection	M3
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	HNBR
Material guide	POM TPE-E High-alloy steel
Material housing	Wrought aluminium alloy
Material piston rod	High-alloy stainless steel