


# Ball valve

## VZBE-1/2-WA-63-T-2-F0304-V15V15

Part number: 8089040

FESTO



## Data sheet

| Feature                                                                       | Value                                                                                        |
|-------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------|
| Design                                                                        | 2-way ball valve                                                                             |
| Type of actuation                                                             | Mechanical                                                                                   |
| Sealing principle                                                             | Soft                                                                                         |
| Mounting position                                                             | optional                                                                                     |
| Type of mounting                                                              | In-line installation                                                                         |
| Connection Process valve                                                      | Weld-on end according to ASME B16.11                                                         |
| Switching position indicator                                                  | Slot direction = flow direction                                                              |
| Flange hole pattern                                                           | F03<br>F04                                                                                   |
| Inside diameter                                                               | 15 mm                                                                                        |
| Nominal size DN                                                               | 15                                                                                           |
| Valve function                                                                | 2/2                                                                                          |
| Flow direction                                                                | Reversible                                                                                   |
| Nominal pressure PN                                                           | 63                                                                                           |
| Breakaway torque at differential pressure, nominal pressure, process valve PN | 7 Nm                                                                                         |
| Based on standard                                                             | ASME B16.11<br>ISO 5211                                                                      |
| Medium                                                                        | Vapour<br>Compressed air to ISO 8573-1:2010 [:-:-]<br>Inert gases<br>Water<br>Neutral fluids |
| Media temperature                                                             | -20 °C...200 °C                                                                              |
| Flow rate Kv                                                                  | 32 m³/h                                                                                      |
| Note on materials                                                             | RoHS-compliant                                                                               |
| LABS (PWIS) conformity                                                        | VDMA24364 zone III                                                                           |

| Feature                        | Value                                                              |
|--------------------------------|--------------------------------------------------------------------|
| Material housing               | Stainless steel casting                                            |
| Material number housing        | 1.4408/CF8M                                                        |
| Material seat seal             | PTFE, modified                                                     |
| Material seals                 | FPM<br>PTFE                                                        |
| Material ball                  | Stainless steel casting                                            |
| Material number ball           | 1.4408/CF8M                                                        |
| Material shaft                 | High-alloy stainless steel                                         |
| Material number shaft          | 1.4401                                                             |
| Product weight                 | 500 g                                                              |
| Approval                       | CRN                                                                |
| Explosion protection           | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Corrosion resistance class CRC | 4 - Very high corrosion stress                                     |