

Parallel kit
EAMM-U-30-V20-28AA-44
Part number: 8093176



Data sheet

Feature	Value
Size	30
Centre-to-centre distance	44 mm
Mounting position	optional
Gear unit ratio	1:1
Max. rotational speed	3000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	0 °C...50 °C
Mass moment of inertia	2.11 kgmm ²
Frictional torque independent of load	0.015 Nm
Transmittable torque	0.05 Nm
Product weight	94 g
Interface code, actuator	V20
Interface code, motor in	28AA
Note on materials	RoHS-compliant