


Axial kit
EAMM-A-D60-80PB
Part number: 8105937



Data sheet

Feature	Value
Mounting position	optional
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transmittable torque	21 Nm
Product weight	1041 g
Interface code, actuator	D60
Interface code, motor in	80PB 80R
Note on materials	RoHS-compliant