

End plate CPX-AP-A-EPL

Part number: 8112476

FESTO



Data sheet

Feature	Value
Dimensions (W x L x H)	(installation dimensions) 30.4 mm x 117.2 mm x 53.6 mm
Grid dimension	50.1 mm
Type of mounting	Direct mounting via through-hole On H-rail via accessories On mounting frame Via through-hole for M5 screw Via through-hole for M6 screw
Product weight	120 g
Mounting position	Any, on H-rail: horizontal
Ambient temperature	-20 °C...50 °C
Note on ambient temperature	Observe ambient temperature derating according to IEC 61131-2:2017
Storage temperature	-20 °C...70 °C
Relative air humidity	5 - 95% Non-condensing
Nominal altitude of use	<= 2000 m ASL (> 79.5 kPa)
Max. installation height	3500 m
Note on max. installation height	> 2000 m ASL (< 79.5 kPa) Observe ambient temperature derating according to IEC 61131-2:2017
Corrosion resistance class CRC	1 - Low corrosion stress
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Note on vibration resistance	SG1 on H-rail SG2 on direct mounting Transport application test with severity class 1 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Note on shock resistance	30 g/11 ms to EN 60068-2-27 SG1 on H-rail SG2 on direct mounting Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Protection class	III
Overvoltage category	II
LABS (PWIS) conformity	VDMA24364-B2-L

Feature	Value
Note on materials	RoHS-compliant Free of halogen Free of phosphoric acid ester
Material end plate	Die-cast aluminium, coated
Material screws	Nickel-plated steel Galvanised steel