

Parallel gripper DHPC-L-16-A-NO-S-2

Part number: 8116811

FESTO



Data sheet

Feature	Value
Size	16
Stroke per gripper jaws	6 mm
Max. replacement accuracy	0.2 mm
Max. angular gripper jaw backlash ax, ay	0 deg
Max. gripper jaw backlash Sz	0 mm
Rotationally symmetrical	0.2 mm
Repetition accuracy, gripper	0.02 mm
Number of gripper jaws	2
Drive system	Pneumatic
Mounting position	optional
Mode of operation	Single-acting Open
Gripper function	Parallel
Gripper force back-up	During opening
Design	Connection direction at side Flat mounting method for gripper fingers Lever Force pilot operated motion sequence
Guide	Ball guide
Position detection	Via proximity switch
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi
Max. operating frequency of gripper	3 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	18 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	17 ms
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Total gripping force, closing, 0.6MPa (6bar, 87 psi)	86.8 N

Feature	Value
Gripper force per gripper jaw, closing, 0.6 MPa (6 bar, 87 psi)	43.4 N
Mass moment of inertia	0.22 kgcm ²
Max. force on gripper jaw Fz static	84 N
Max. torque at gripper Mx static	0.94 Nm
Max. torque at gripper My static	0.71 Nm
Max. torque at gripper Mz static	0.71 Nm
Product weight	129 g
Type of mounting	Direct mounting via through-hole Direct mounting via thread Via through-hole and dowel pin Via female thread and dowel pin Either:
Pneumatic connection	M3
Note on materials	RoHS-compliant
Material housing	Anodised aluminium
Material gripper jaws	High-alloy stainless steel