

# Parallel gripper DHPC-...-40-A-

Part number: 8116734

**FESTO**



## Data sheet

Feature	Value
Size	40
Stroke per gripper jaws	15 mm
Max. replacement accuracy	0.2 mm
Max. angular gripper jaw backlash ax, ay	0 deg
Max. gripper jaw backlash Sz	0 mm
Rotationally symmetrical	0.2 mm
Repetition accuracy, gripper	0.02 mm
Number of gripper jaws	2
Drive system	Pneumatic
Mounting position	optional
Mode of operation	Double-acting Single-acting Closed Open
Gripper function	Parallel
Gripper force back-up	None
Design	Connection via mounting spigot Connection direction at side Connection direction downwards Flat mounting method for gripper fingers Lever Side mounting method for gripper fingers Standard mounting method for gripper fingers Force pilot operated motion sequence
Guide	Ball guide
Position detection	Via proximity switch
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi
Max. operating frequency of gripper	1 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	158 ms...370 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	67 ms...153 ms
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)

Feature	Value
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Total gripping force, opening, 0.6MPa (6bar, 87 psi)	733.5 N...777.2 N
Total gripping force, closing, 0.6MPa (6bar, 87 psi)	675 N...717.2 N
Gripper force per gripper jaw, opening, 0.6 MPa (6 bar, 87 psi)	366.8 N...388.6 N
Gripper force per gripper jaw, closing, 0.6 MPa (6 bar, 87 psi)	337.5 N...358.6 N
Mass moment of inertia	14.87 kgcm <sup>2</sup> ...17.06 kgcm <sup>2</sup>
Max. force on gripper jaw Fz static	351.5 N
Max. torque at gripper Mx static	16.15 Nm
Max. torque at gripper My static	9.55 Nm
Max. torque at gripper Mz static	9.55 Nm
Product weight	1396 g...1740 g
Type of mounting	Direct mounting via through-hole Direct mounting via thread On mounting frame Via through-hole and dowel pin Via female thread and dowel pin Either:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material housing	Anodised aluminium
Material gripper jaws	High-alloy stainless steel