


PROFINET Interface CPX-AP-A-PN-CU

Part number: 8129245

FESTO



Data sheet

Feature	Value
Dimensions (W x L x H)	(incl. interlinking block) 50.1 mm x 107.3 mm x 94.2 mm
Grid dimension	50.1 mm
Type of mounting	Screw-clamped
Max. number of modules	80
Product weight	167 g
Mounting position	optional
Ambient temperature	-20 °C...50 °C
Note on ambient temperature	Observe ambient temperature derating according to IEC 61131-2:2017
Storage temperature	-20 °C...70 °C
Relative air humidity	5 - 95% Non-condensing
Nominal altitude of use	<= 2000 m ASL (> 79.5 kPa)
Max. installation height	3500 m
Note on max. installation height	> 2000 m ASL (< 79.5 kPa) Observe ambient temperature derating according to IEC 61131-2:2017
Corrosion resistance class CRC	1 - Low corrosion stress
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Note on vibration resistance	SG1 on H-rail SG2 on direct mounting Transport application test with severity class 1 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Note on shock resistance	30 g/11 ms to EN 60068-2-27 SG1 on H-rail SG2 on direct mounting Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Protection class	III
Pollution degree	2
Overvoltage category	II
Max. cable length	100 m PROFINET
LABS (PWIS) conformity	VDMA24364-B2-L
Fire test material	UL94 V-0 (housing)

Feature	Value
Note on materials	RoHS-compliant Free of halogen Free of phosphoric acid ester
Material cover	PBT-reinforced
Material flange	Die-cast zinc, nickel-plated
Material screws	Nickel-plated steel
Material threaded sleeve	High-alloy stainless steel
Material seals	NBR
Material o-ring	FPM
Diagnostics via LED	Diagnostics per module PROFINET communication Power supply, electronics/sensors Load power supply System diagnostics Service required
Diagnostics via bus	APDD invalid Load switch-off Communication fault Electronics/sensors overvoltage Load overvoltage Electronics/sensors undervoltage Load undervoltage
Fieldbus interface	Ethernet
Field bus, protocol	LLDP MRP, MRPD (ring redundancy) PROFINET FSU PROFINET I&M0 ..3 PROFINET IRT PROFINET RT PROFINET shared device S2 system redundancy SNMP
Field bus, connection type	2x socket
Field bus, connection system	RJ45 to IEC 61076-3-117 (V14)
Field bus, connection pattern	8
Field bus interface, electrical isolation	yes
Field bus interface, transmission rate	100 Mbit/s
Fieldbus interface, note on transmission rate	100 Mbit, fast switching Ethernet
Max. address volume, inputs	1024 Byte
Max. address volume, outputs	1024 Byte
Module parameters	Configuration of voltage monitoring load supply PL
Internal cycle time	< 1 ms
Configuration support	GSDML file
Communication interface, function	System communication XF20 OUT
Communication interface, connection type	Socket
Communication interface, connection technology	M8x1, D-coded according to EN 61076-2-114
Communication interface, number of pins/wires	4
Communication interface, protocol	AP
Communication interface, shielding	yes
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
Note on nominal operating voltage DC	Protected Extra-Low-Voltage to IEC 60204-1
Nominal operating voltage DC of load	24 V
Permissible voltage fluctuation of load	± 25 %
Nominal DC operating voltage, electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	± 25%
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 80 mA
Intrinsic current consumption at nominal operating voltage load	Typically 4 mA

Feature	Value
Power failure bridging	10 ms
Potential separation between the supply voltages electronics/sensor technology and load/valves	Yes
Reverse polarity protection	yes