

End plate CPX-AP-A-EPLI-S

Part number: 8129249

FESTO



Data sheet

Feature	Value
Dimensions (W x L x H)	(installation dimensions) 48.4 mm x 117.2 mm x 61.5 mm
Grid dimension	50.1 mm
Type of mounting	Direct mounting via through-hole On H-rail via accessories On mounting frame Via through-hole for M5 screw Via through-hole for M6 screw
Product weight	256 g
Mounting position	Any, on H-rail: horizontal
Ambient temperature	-20 °C...50 °C
Note on ambient temperature	Observe ambient temperature derating according to IEC 61131-2:2017
Storage temperature	-20 °C...70 °C
Relative air humidity	5 - 95% Non-condensing
Nominal altitude of use	<= 2000 m ASL (> 79.5 kPa)
Max. installation height	3500 m
Note on max. installation height	> 2000 m ASL (< 79.5 kPa) Observe ambient temperature derating according to IEC 61131-2:2017
Corrosion resistance class CRC	1 - Low corrosion stress
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Note on vibration resistance	SG1 on H-rail SG2 on direct mounting Transport application test with severity class 1 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Note on shock resistance	30 g/11 ms to EN 60068-2-27 SG1 on H-rail SG2 on direct mounting Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Protection class	III
Pollution degree	2

Feature	Value
Overvoltage category	II
Max. cable length	50 m system communication
LABS (PWIS) conformity	VDMA24364-B2-L
Fire test material	UL94 V-0 (housing)
Note on materials	RoHS-compliant Free of halogen Free of phosphoric acid ester
Material housing	Die-cast aluminium, coated
Material cover	PBT-reinforced
Material screws	Nickel-plated steel Galvanised steel
Material seals	PU foam
Material o-ring	FPM
Diagnostics via LED	Diagnostics per module Power supply, electronics/sensors Load power supply
Diagnostics per internal communication	Load switch-off Communication fault Electronics/sensors overvoltage Load overvoltage Electronics/sensors undervoltage Load undervoltage
Max. address volume, inputs	2048 Byte
Max. address volume, outputs	2048 Byte
Communication interface, function	System communication XF10 IN / XF20 OUT
Communication interface, connection type	2x socket
Communication interface, connection technology	M8x1, D-coded according to EN 61076-2-114
Communication interface, number of pins/cores	4
Communication interface, protocol	AP
Communication interface, shielding	yes
Power supply, function	Incoming electronics/sensors and load
Power supply, connection type	Plugs
power supply, connection system	M8x1, A-coded to EN 61076-2-104
Power supply, number of pins/wires	4
Power transmission, function	Outgoing electronics/sensors and load
Power transmission, connection type	Socket
Power transmission, connection technology	M8x1, A-coded to EN 61076-2-104
Power transmission, number of pins/wires	4
Note regarding operating voltage	SELV/PELV fixed power supplies required Note voltage drop
Note on nominal operating voltage DC	2x24 V [XD1,PS,PL] Protected Extra-Low-Voltage to IEC 60204-1
Nominal operating voltage DC of load	24 V
Permissible voltage fluctuation of load	± 25 %
Nominal DC operating voltage, electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	± 25%
Power supply, conductor diameter	0.5 mm ²
Nominal current	4 A
Max. power supply	2 x 4 A (external fuse required)
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 41 mA
Power failure bridging	10 ms
Potential separation between the supply voltages electronics/sensor technology and load/valves	Yes
Reverse polarity protection	yes