


Adapter plate VABA-C13-100-1-F90-G12

Part number: 8141664

FESTO



Data sheet

| Feature | Value |
|---------------------------------------|--|
| Size | 240 300 480 700 900 |
| Mounting position | optional |
| Design | Adapter for rotary drive |
| Valve connection conforms to standard | VDI/VDE 3847-2 |
| Operating pressure | 0 MPa...0.9 MPa 0 bar...9 bar |
| Explosion protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:7:-] Inert gases |
| Note on operating and pilot medium | Lubricated operation not possible |
| Corrosion resistance class CRC | 3 - high corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Media temperature | -40 °C...80 °C |
| Ambient temperature | -40 °C...80 °C |
| Product weight | 2225 g |
| Type of mounting | With accessories |
| Pneumatic connection | Sub-base design, airing |
| Pneumatic connection, port 1 | G1/2 |
| Pneumatic connection, port 2 | Internal |
| Pneumatic connection, port 3 | G1/2 |
| Pneumatic connection, port 4 | Internal |
| Note on materials | RoHS-compliant |
| Material cover | Smooth-anodised wrought aluminium alloy (20 µm) |
| Material seals | EPDM NBR |
| Material housing | Smooth-anodised wrought aluminium alloy (20 µm) |
| Material screws | High-alloy stainless steel |